



- 技术指标 (Technical Index):
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。  
(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
  2. 锁扣窗口: 2~3PIN为1个, ≥4PIN为2个。(Lock Configuration: 2 to 3Pin is 1, ≥4Pin is 2)
  3. 不同Pin位吸盖加入/取出力有差异, 实属正常现象。  
(It is normal that there are differences between suction cap and suction cap at different Pin positions)
  4. 温度范围 (Temperature range): -65° C~125° C.
  5. 额定电压 (Rated voltage): 125V, AC/DC (=等效).
  6. 接触电阻 (Contact resistance): ≤0.02Ω.
  7. 绝缘电阻 (Insulation resistance): ≥100MΩ
  8. 产品料号 (Product Material No.):

CKT	DIM A	DIM B	DIM C	DIM D
2	1.25	3.25	7.30	7.50
3	2.50	4.50	8.55	8.75
4	3.75	5.75	9.80	10.00
5	5.00	7.00	11.05	11.25
6	6.25	8.25	12.30	12.50
7	7.50	9.50	13.55	13.75
8	8.75	10.75	14.80	15.00
9	10.00	12.00	16.05	16.25
10	11.25	13.25	17.30	17.50
11	12.50	14.50	18.55	18.75
12	13.75	15.75	19.80	20.00
13	15.00	17.00	21.05	21.25
14	16.25	18.25	22.30	22.50
15	17.50	19.50	23.55	23.75
16	18.75	20.75	24.80	25.00
17	20.00	22.00	26.05	26.25
18	21.25	23.25	27.30	27.50
19	22.50	24.50	28.55	28.75
20	23.75	25.75	29.80	30.00

APPROVALS		DATE	PART NO.	
DRAWN	G.M.Chen	2015/7/17	1.25-□□□□	
CHECKED			TITLE:	
APPROVALS			1.25 Pitch 立式	
TOLERANCES ARE		ANGLE	UNIT: mm	SCALE: 1:1
0.1	±0.05	±2°		SHEET 1 OF 1
0.2	±0.10			PROJ.
0.5	±0.10			
ECN NO.	REV.	DATE.	DESCRIPTION.	NEW
	A			

