



技术指标 (Technical Index):

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。  
(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena)
2. 锁扣窗口: 2~3PIN为1个, ≥4PIN为2个。(Lock Configuration: 2 to 3Pin is 1, ≥4Pin is 2)
3. 不同Pin位吸盖加入/取出力有差异, 实属正常现象。  
(It is normal that there are differences between suction cap and suction cap at different Pin positions)
4. 温度范围 (Temperature range): -65° C~125° C.
5. 额定电压 (Rated voltage): 125V, AC/DC (=等效).
6. 接触电阻 (Contact resistance): ≤0.02Ω.
7. 绝缘电阻 (Insulation resistance): ≥100MΩ
8. 产品料号 (Product Material No.):



| CKT | DIM A | DIM B | DIM C | DIM D |
|-----|-------|-------|-------|-------|
| 2   | 1.25  | 3.25  | 7.30  | 7.50  |
| 3   | 2.50  | 4.50  | 8.55  | 8.75  |
| 4   | 3.75  | 5.75  | 9.80  | 10.00 |
| 5   | 5.00  | 7.00  | 11.05 | 11.25 |
| 6   | 6.25  | 8.25  | 12.30 | 12.50 |
| 7   | 7.50  | 9.50  | 13.55 | 13.75 |
| 8   | 8.75  | 10.75 | 14.80 | 15.00 |
| 9   | 10.00 | 12.00 | 16.05 | 16.25 |
| 10  | 11.25 | 13.25 | 17.30 | 17.50 |
| 11  | 12.50 | 14.50 | 18.55 | 18.75 |
| 12  | 13.75 | 15.75 | 19.80 | 20.00 |
| 13  | 15.00 | 17.00 | 21.05 | 21.25 |
| 14  | 16.25 | 18.25 | 22.30 | 22.50 |
| 15  | 17.50 | 19.50 | 23.55 | 23.75 |
| 16  | 18.75 | 20.75 | 24.80 | 25.00 |
| 17  | 20.00 | 22.00 | 26.05 | 26.25 |
| 18  | 21.25 | 23.25 | 27.30 | 27.50 |
| 19  | 22.50 | 24.50 | 28.55 | 28.75 |
| 20  | 23.75 | 25.75 | 29.80 | 30.00 |

|                     |      |       |              |                |        |        |
|---------------------|------|-------|--------------|----------------|--------|--------|
| ECN NO.             | REV. | DATE. | DESCRIPTION. | CHANGE.        | CHECK. | APPRO. |
|                     | A    |       | NEW          |                |        |        |
| APPROVALS           |      |       | DATE         | TOLERANCES ARE |        |        |
| DRAWN G.M.Chen      |      |       | 2015/7/17    | 30~0.15        | ±0.30  | ANGLE  |
| CHECKED             |      |       |              | 0.~0.10        | ±0.20  | ±2°    |
| APPROVALS           |      |       |              | 0.~0.10        | ±0.10  | ±2°    |
| TITLE:              |      |       | PART NO.     | DRAWING NO.    |        |        |
| 1.25 Pitch 立式       |      |       |              | SCALE: 1:1     |        |        |
| DEALON 德之隆          |      |       |              | SHEET 1 OF 1   |        |        |
| ELECTRONICS CO.,LTD |      |       |              | PROJ.          |        |        |