






LOCK CONFIGURATION (锁扣结构)



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 锁扣窗口: 2~3PIN为1个, ≥4PIN为2个。
3. 温度范围: -40~85°C。
4. 额定电压: 125V, AC。
5. 接触电阻: ≤5mΩ (Initial) per contact, ≤20mΩ Change allowed.
6. 绝缘电阻: ≥100MΩ。



适用线路板

CKT	DIM A	DIM B	DIM C	DIM D
2	1.25	3.05	7.25	7.25
3	2.50	4.30	8.50	8.50
4	3.75	5.55	9.75	9.75
5	5.00	6.80	11.00	11.00
6	6.25	8.05	12.25	12.25
7	7.50	9.30	13.50	13.50
8	8.75	10.55	14.75	14.75
9	10.00	11.80	16.00	16.00
10	11.25	13.05	17.25	17.25
11	12.50	14.30	18.50	18.50
12	13.75	15.55	19.75	19.75
13	15.00	16.80	21.00	21.00
14	16.25	18.05	22.25	22.25
15	17.50	19.30	23.50	23.50
16	18.75	20.55	24.75	24.75
17	20.00	21.80	26.00	26.00
18	21.25	23.05	27.25	27.25
19	22.50	24.30	28.50	28.50
20	23.75	25.55	29.75	29.75

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS	DATE	APPROVALS	DATE
DRAWN	G.M.Chen	2015/7/17	
CHECKED			
APPROVALS			

TOLERANCES ARE

30~90°	±0.50	ANGLE	±2°
0~30	±0.20		
0~10	±0.15		
~5	±0.10		

PART NO. 1.25-□□□□□□□□

UNIT: mm SCALE: 1:1 SHEET 1 OF 1

DRAWING NO. PROJ.

DEALON 德之隆
ELECTRONICS CO.,LTD

1.25 Pitch 卧式