




Poles	Dimensions(mm)		
	A	B	C
02	1.25	5.75	4.95
03	2.50	7.00	6.20
04	3.75	8.25	7.45
05	5.00	9.50	8.70
06	6.25	10.75	9.95
07	7.50	12.00	11.20
08	8.75	13.25	12.45
09	10.00	14.50	13.70
10	11.25	15.75	14.95
11	12.50	17.00	16.20
12	13.75	18.25	17.45



PCB Layout(Pattern side)



**NOTE:**  
 Voltage rating: 50V AC/DC  
 Current rating: 1A AC / DC  
 Withstanding voltage: 500V AC/minute  
 Temperature range: -40°C~+110°C  
 Insulation resistance: ≥100MΩ  
 Contact resistance: ≤20mΩ  
 After environmental test: ≤50mΩ

APPROVALS		DATE	ELECTRONICS CO.,LTD	
DRAWN	G.M.Chen	2015/5/22	DEALON 德之隆®	
CHECKED			Connector	
APPROVALS			PART NO.	L125WS-XXPW
TOLERANCES ARE		ANGLE	UNIT: mm	SCALE: 1:1
±0.30	±0.20	±2°	DRAWING NO.	SHEET 1 OF 1
±0.10	±0.15			PROJ.
ECN NO.	REV.	DATE.	DESCRIPTION.	
	A		NEW	