



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 适用线规: AWG#28~#22。
4. 额定电压: 250V DC/AC (rms)。
5. 额定电流: 3.0A。
6. 接触电阻: $\leq 20\text{m}\Omega$ 。
7. 耐压值: 1000V AC/minute。
8. 绝缘电阻: $\geq 1000\text{M}\Omega$ 。

CKT	DIM A	DIM B	DIM C
2	2.50	7.50	10.00
3	5.00	10.00	12.50
4	7.50	12.50	15.00
5	10.00	15.00	17.50
6	12.50	17.50	20.00
7	15.00	20.00	22.50
8	17.50	22.50	25.00
9	20.00	25.00	27.50
10	22.50	27.50	30.00
11	25.00	30.00	32.50
12	27.50	32.50	35.00
13	30.00	35.00	37.50
14	32.50	37.50	40.00
15	35.00	40.00	42.50
16	37.50	42.50	45.00

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	XH-□□PWB	
CHECKED			2.50 Pitch 卧式	
APPROVALS			TOLERANCES ARE	
			30~40 ±0.50	ANGLE ±2°
			40~50 ±0.20	
			50~60 ±0.15	
			60~10 ±0.10	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.
	A		NEW	

DEALON 德之隆
ELECTRONICS CO.,LTD