



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: -25° C~85° C.
3. 适用线规: AWG#28~#22.
4. 额定电压: 250V DC/AC(rms).
5. 额定电流: 3.0A.
6. 接触电阻: ≤20mΩ.
7. 耐压值: 1000V AC/minute.
8. 绝缘电阻: ≥1000MΩ.

CKT	DIM A	DIM B	DIM C
2	2.50	7.50	10.00
3	5.00	10.00	12.50
4	7.50	12.50	15.00
5	10.00	15.00	17.50
6	12.50	17.50	20.00
7	15.00	20.00	22.50
8	17.50	22.50	25.00
9	20.00	25.00	27.50
10	22.50	27.50	30.00
11	25.00	30.00	32.50
12	27.50	32.50	35.00
13	30.00	35.00	37.50
14	32.50	37.50	40.00
15	35.00	40.00	42.50
16	37.50	42.50	45.00

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	EVALON 德之隆 ELECTRONICS CO.,LTD	
CHECKED			TITLE: 2.50 Pitch 卧式	
APPROVALS			PART NO.	XH-□□PWB
TOLERANCES ARE		30~40±0.50	±0.50	ANGLE
		40~50±0.20	±0.20	±2°
		50~100±0.15	±0.15	
		≥100±0.10	±0.10	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.
	A		NEW	
				CHECK.
				APPRO.