



- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 工作温度: -25°C ~ +85°C。
 3. 适用线规: AWG#28~#22。
 4. 额定电压: 250V DC/AC(rms)。
 5. 额定电流: 3.0A。
 6. 接触电阻: ≤20mΩ。
 7. 耐压值: 1000V AC/minute。
 8. 绝缘电阻: ≥1000MΩ。

CKT	DIM A	DIM B	DIM C
2	2.50	7.50	10.00
3	5.00	10.00	12.50
4	7.50	12.50	15.00
5	10.00	15.00	17.50
6	12.50	17.50	20.00
7	15.00	20.00	22.50
8	17.50	22.50	25.00
9	20.00	25.00	27.50
10	22.50	27.50	30.00
11	25.00	30.00	32.50
12	27.50	32.50	35.00
13	30.00	35.00	37.50
14	32.50	37.50	40.00
15	35.00	40.00	42.50
16	37.50	42.50	45.00

2P 结构

DEALON 德隆 ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE						
APPROVALS			DATE	PART NO.		
DRAWN	G.M.Chen	2015/7/17	TITLE: 2.50 Pitch 立式			
CHECKED			XH-□□□□			
APPROVALS			SCALE: 1:1			
DRAWING NO.			SHEET 1 OF 1			
DRAWING NO.			PROJ.			