



- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -25°C~85°C。
 3. 额定电压: 100V, AC/DC。
 4. 接触电阻: ≤0.02Ω。
 5. 绝缘电阻: ≥500MΩ。
 6. 额定电流: 1A, AC/DC。

CKT	DIM A	DIM B
2	1.50	6.00
3	3.00	7.50
4	4.50	9.00
5	6.00	10.50
6	7.50	12.00
7	9.00	13.50
8	10.50	15.00
9	12.00	16.50
10	13.50	18.00
11	15.00	19.50
12	16.50	21.00
13	18.00	22.50
14	19.50	24.00
15	21.00	25.50
16	22.50	27.00
17	24.00	28.50
18	25.50	30.00
19	27.00	31.50
20	28.50	33.00

APPROVALS		DATE	DEALON 德之隆 ELECTRONICS CO.,LTD	
DRAWN	G.M.Chen	2015/7/17	TITLE: 1.50 Pitch 立式 PART NO. ZH-XXPS UNIT: mm SCALE: 1:1 SHEET 1 OF 1	
CHECKED				
APPROVALS				

ECN NO.	REV.	DATE	DESCRIPTION	CHANGE	CHECK	APPRO.	TOLERANCES ARE	30°±0.1°	±0.30	ANGLE	PART NO.	SCALE: 1:1	SHEET 1 OF 1
	A		NEW				±0.20	±0.20	±2°		ZH-XXPS	1:1	1 OF 1
							±0.10	±0.10					