





版次	日期	变更内容	变更单号	变更者
1.0	13.8.5	原始版本		

20	19.0	22.0	21.3
19	18.0	21.0	20.3
18	17.0	20.0	19.3
17	16.0	19.0	18.3
16	15.0	18.0	17.3
15	14.0	17.0	16.3
14	13.0	16.0	15.3
13	12.0	15.0	14.3
12	11.0	14.0	13.3
11	10.0	13.0	12.3
10	9.0	12.0	11.3
9	8.0	11.0	10.3
8	7.0	10.0	9.3
7	6.0	9.0	8.3
6	5.0	8.0	7.3
5	4.0	7.0	6.3
4	3.0	6.0	5.3
3	2.0	5.0	4.3
2	1.0	4.0	3.3
Poles	A	B	C



P.C.B LAYOUT REF

技术参数

额定电压: 50V AC DC
 额定电流: 1A; AC, DC
 耐压值: 200V. min/AC
 绝缘电阻: 100MΩ, Min
 接触电阻: 20mΩ Max
 耐压 Withstanding Voltang 500V

材料

工作温度: -25°C ~ +85°C
 间距: 1.0mm
 外壳: LCP米色
 插针: 磷铜

1. 0T-立贴		图号	
绘制		比例	
审查		单位	mm
核准		页次	of
供应商			