



孔位 OKT NO.	DIM A	DIM B	DIM C	DIM D
16	30.00	36.00	32.80	28.90
15	28.00	34.00	30.80	26.90
14	26.00	32.00	28.80	24.90
13	24.00	30.00	26.80	22.90
12	22.00	28.00	24.80	20.90
11	20.00	26.00	22.80	18.90
10	18.00	24.00	20.80	16.90
9	16.00	22.00	18.80	14.90
8	14.00	20.00	16.80	12.90
7	12.00	18.00	14.80	10.90
6	10.00	16.00	12.80	8.90
5	8.00	14.00	10.80	6.90
4	6.00	12.00	8.80	4.90
3	4.00	10.00	6.80	2.90
2	2.00	8.00	4.80	2.70

技术要求Notes:
1.外观质量Appearance quality:
 a.金属表面镀层不能有明显损伤:
 Coating on metal surface can not be damaged obviously;
 b.塑壳表面不能有明显的变形或开裂:
 No obvious deformation or cracking can be observed on the surface of the Housing;
 c.产品表面应保持清洁:
 Product surface should be kept clean;
2.工作温度 Working temperature: -25℃~+105℃;
3.额定电压 Voltage Rating : Max 250V (AC/Effective value rms)/DCI;
4.额定电流 Current Rating: Max 2A (AC/Effective value rms)/DCI;
5.接触电阻 Contact resistance: Max 20 mΩ
6.绝缘电阻 Insulation resistance: Min 1000MΩ;
7.耐压 Withstanding voltage: 1000V AC(50 Hz, Effective value: 1 min);
8.环保要求应符合RoHS标准
 Environmental requirements should meet RoHS standards.

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE
DRAWN	G.M.Chen	2015/7/17
CHECKED		
APPROVALS		

TOLERANCES ARE		ANGLE	UNIT:	SCALE:	SHEET
30 ^{±0.15}	±0.30		mm	1:1	1 OF 1
10 ^{±0.10}	±0.20				
5 ^{±0.05}	±0.15	±2°			

DRAWING NO.		PART NO.		TITLE:	
L200HY-XXPWB		L200HY-XXPWB		CONNECTOR	

EVALON 德之隆®		ELECTRONICS CO.,LTD	
-------------	--	---------------------	--