



P. C. B LOYOCT

- 技术要求Notes:**
- 1.外观质量 Appearance quality:
    - a.金属表面镀层不能有明显损伤: Coating on metal surface can not be damaged obviously;
    - b.塑壳表面不能有明显的变形或开裂: No obvious deformation or cracking can be observed on the surface of the Housing;
    - c.产品表面应保持清洁: Product surface should be kept clean;
  - 2.工作温度 Working temperature: -25℃~+105℃;
  - 3.额定电压 Voltage Rating: Max 250V [AC/Effective value ms)/DC];
  - 4.额定电流 Current Rating: Max 2A [AC/Effective value ms)/DC];
  - 5.接触电阻 Contact resistance: Max 20 mΩ
  - 6.绝缘电阻 Insulation resistance: Min 1000MΩ;
  - 7.耐压 Withstanding voltage: 1000V AC(50 Hz. Effective value: 1 min);
  - 8.环保要求应符合RoHS标准 Environmental requirements should meet RoHS standards.

Pin	A	B	C
2	2.50	10.00	8.30
3	5.00	12.50	10.80
4	7.50	15.00	13.30
5	10.00	17.50	15.80
6	12.50	20.00	18.30
7	15.00	22.50	20.80
8	17.50	25.00	23.30
9	20.00	27.50	25.80
10	22.50	30.00	28.30
11	25.00	32.50	30.80
12	27.50	35.00	33.30
13	30.00	37.50	35.80
14	32.50	40.00	38.30
15	35.00	42.50	40.80
16	37.50	45.00	43.30

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

  

APPROVALS		DATE
DRAWN	G.M.Chen	2015/7/17
CHECKED		
APPROVALS		

  

TOLERANCES ARE		ANGLE	SCALE	SHEET
30~40	±0.30	±2°	1:1	1 OF 1
10~30	±0.20			
5~10	±0.15			
~5	±0.10			

  

TITLE:		PART NO.	SCALE:	SHEET
CONNECTOR		L254XHB-XXPW	1:1	1 OF 1
DRAWING NO.		PROJ.		

  

**DEALON 德之隆**  
ELECTRONICS CO.,LTD