


P. C. B LAYOUT

- 技术要求Notes:
- 外观质量 Appearance quality:
 - 金属表面镀层不能有明显损伤; Coating on metal surface can not be damaged obviously;
 - 塑壳表面不能有明显的变形或开裂; No obvious deformation or cracking can be observed on the surface of the Housing;
 - 产品表面应保持清洁; Product surface should be kept clean;
 - 工作温度 Working temperature: -25℃~+105℃;
 - 额定电压 Voltage Rating: Max 250V [AC(Effective value rms)/DC];
 - 额定电流 Current Rating: Max 2A [AC(Effective value rms)/DC];
 - 接触电阻 Contact resistance: Max 20 mΩ
 - 绝缘电阻 Insulation resistance: Min 1000MΩ;
 - 耐压 Withstanding voltage: 1000V AC(50 Hz, Effective value: 1 min);
 - 环保要求应符合RoHS标准 Environmental requirements should meet RoHS standards.



Pin	A	B	C
2	2.50	10.00	8.30
3	5.00	12.50	10.80
4	7.50	15.00	13.30
5	10.00	17.50	15.80
6	12.50	20.00	18.30
7	15.00	22.50	20.80
8	17.50	25.00	23.30
9	20.00	27.50	25.80
10	22.50	30.00	28.30
11	25.00	32.50	30.80
12	27.50	35.00	33.30
13	30.00	37.50	35.80
14	32.50	40.00	38.30
15	35.00	42.50	40.80
16	37.50	45.00	43.30

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE
DRAWN	G.M.Chen	2015/7/17
CHECKED		
APPROVALS		

TOLERANCES ARE		30~0.15	±0.30	ANGLE
10~30	±0.20	9~10	±0.15	±2°
~5	±0.10			

TITLE:		PART NO.		SCALE:	SHEET
ELECTRONICS CO.,LTD		L254XHB-XXPS		1:1	1 OF 1
CONNECTOR		DRAWING NO.		PROJ.	