



**SPECIFICATIONS**

- 1.Voltage rating: 250V AC, DC
  - 2.Current rating: 7A, AC, DC
  - 3.Withstanding Voltage: 1500V AC/minute
  - 4.Insulation resistance:1000MΩ min
  - 5.Temperature range: -25°C--+85°C
  - 6.Contact resistance: 10mΩ max
- WAFER
- Housing Material: LCP UL 94V0  
 Pin Material: Phosphor Bronze or Brass  
 Contact Area Plating: Plated Tin or Plated Gold

Pin	A	B	C
2	3.96	9.9	11.88
3	7.92	13.86	15.84
4	11.88	17.82	19.80
5	15.84	21.78	23.76
6	19.80	25.74	27.72
7	23.76	29.70	31.68
8	27.72	33.66	35.64
9	31.68	37.62	39.60
10	35.64	41.58	43.56
10	39.60	45.54	47.52
12	43.56	49.50	51.48

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2014/11/26	ELECTRONICS CO.,LTD	
CHECKED			TITLE: CONNECTOR	
APPROVALS			PART NO.	L396VH-XXPS
TOLERANCES ARE		30 <sup>±0.15</sup>	±0.30	ANGLE
		10 <sup>±0.10</sup>	±0.20	UNIT: mm
		5 <sup>±0.05</sup>	±0.15	SCALE: 1:1
				SHEET 1 OF 1
CHANGE.	CHECK.	APPRO.	DRAWING NO.	PROJ.
ECN NO.	REV.	DATE.	DESCRIPTION.	
	A		NEW	