



SPECIFICATIONS

- 1.Voltage rating: 250V AC, DC
 - 2.Current rating: 7A, AC, DC
 - 3.Withstanding Voltage: 1500V AC/minute
 - 4.Insulation resistance:1000MΩ min
 - 5.Temperature range: -25°C--+85°C
 - 6.Contact resistance: 10mΩ max
- WAFER
- Housing Material: LCP UL 94V0
 Pin Material: Phosphor Bronze or Brass
 Contact Area Plating: Plated Tin or Plated Gold

Pin	A	B	C
2	3.96	9.9	11.88
3	7.92	13.86	15.84
4	11.88	17.82	19.80
5	15.84	21.78	23.76
6	19.80	25.74	27.72
7	23.76	29.70	31.68
8	27.72	33.66	35.64
9	31.68	37.62	39.60
10	35.64	41.58	43.56
10	39.60	45.54	47.52
12	43.56	49.50	51.48

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2014/11/26	ELECTRONICS CO.,LTD	
CHECKED			CONNECTOR	
APPROVALS			L396VH-XXPS	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	SHEET	PROJ.
	A		NEW				30 ^{±0.15} 10 ^{±0.20} 5 ^{±0.13}	±2°	mm	1:1	1 OF 1	