



1. Electrical Characteristics

- 1.1 Impedance: 50 Ohm
- 1.2 Working Frequency: DC - 6 GHz
- 1.3 S.W.R. :  $\leq 2.0$
- 1.4 Working Voltage: 335V / max
- 1.5 Insulation Resistance: 1000 Mohm
- 1.6 Contact Resistance: Center Contact: 5 mohm
- 1.7 Outer Contact:  $\leq 2.5$  mohm

2. Environmental

- 2.1 Working Temperature Range:  $-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$

	<b>HX</b> 深圳市环协科技有限公司 ShenZhenHuanXieTechnologyco.ltd			
	<b>Tolerance</b> 未标注公差:	C/U NO. 客户编号	Part Name. 品名/规格	SMA JCAK S/T FOR PCB
	.X ±0.2	<b>Material.</b> 材質	C/U Part No. 客户料號	
	.XX ±0.10	<b>Finish.</b> 處理	PartNo. 料號	HX-SMA-P-9671
	.XXX ±0.05	<b>Scale.</b> 比例	Draw . 繪圖	<b>Check.</b> 校對 <b>App.</b> 核准
未标注角度公差: $\pm 1^{\circ}$	<b>REV.</b> 版本/次	A/O	琚芬	
	<b>Unite.</b> 單位:	mm	2022.08.10	

4	螺牙本体	黄铜 镀金	1	Rev.	Date.	变更单号 ECN No.	变更者	Description. 内容
3	PIN针	黄铜 镀金	1					
2	绝缘体	PTFE 白色	1					
1	四角本体	黄铜 镀金	1					
部件 序号	部件品名	材料	用量	Rev.	Date.	变更单号 ECN No.	变更者	Description. 内容