



1. Electrical Characteristics

- 1.1 Impedance: 50 Ohm
- 1.2 Working Frequency: DC - 8 GHz
- 1.3 S.W.R. : ≤ 2.0
- 1.4 Working Voltage: 335V / max
- 1.5 Insulation Resistance: 1000 Mohm
- 1.6 Contact Resistance: Center Contact: 5 mohm
- 1.7 Outer Contact: ≤ 2.5 mohm

2. Environmental

- 2.1 Working Temperature Range: $-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$

5	绝缘体	PTFE 白色	1
4	IPX头	磷铜 镀镍	1
3	PIN针	黄铜 镀金	1
2	绝缘体	PTFE 白色	1
1	螺牙本体	黄铜 镀镍	1

Rev.	Date.	ECN No.	Rev.	Date.	ECN No.	Rev.	Date.	ECN No.	Description. 内容

	Tolerance 未標注公差:			深圳市环协科技有限公司 ShenZhenHuanXieTechnologyco.ltd	
	.X	± 0.2	C/U NO. 客戶編號	Part Name. 品名/規格	TNC转IPEX端子测试头
.XX	± 0.10	Material. 材質	C/U Part No. 客戶料號		
.XXX	± 0.05	Finish. 處理	PartNo. 料號	HX-TNC-IPX-8881	
未標注角度公差: $\pm 1^{\circ}$		Scale. 比例	1:1	Draw . 繪圖	Check. 校對
		REV. 版本/次	A/0		App. 核准
		Unit. 單位:	mm		