


# PARTS NUMBER SYSTEM

JAMICON®



Series			Code	Type	Description	CAP (μF)	Code	Tolerance (%)	Code	Voltage (W.V.)	Code	Diameter (φ)	Code	Length (L)	Code	Code	Description
PS	SS	UK	R	Radial	Bulk	0.1	OR1	+10	K	2.5	0E	3	A	11	11	W	Without Sleeve
PT	SH	NC				0.22	R22	-10		4	0G	3.8	S	11.5	BB		Customer Assign
PH	SL	RV	P	Radial	Taping (Ammo Pack)	0.33	R33	+15	L	6.3	0J	4	C	12.5	BC	1~9	Customer Assign
PC	NS	LP				0.47	R47	-15		10	1A	5	D	31.5	DB		
PF	<b>SK</b>	HP	C	Radial	Lead Cut	1	010	+20	M	13	1P	6	W	35.5	DF	a~	Brand
PB	SM	LS				2.2	2R2	-20		16	<b>1C</b>	6.3	E	100	1H		
CS	TK	HS	F	Radial	Lead Forming Cut	3.3	3R3	+100	P	20	1D	7	Y	110	1A		
CA	TM	HM				4.7	4R7	-0		25	1E	8	<b>F</b>	115	1K		
CN	NK	LT	B	Radial	Lead Forming Only	10	100	+30	Q	35	1V	10	G	120	1B		
CR	LK	LL				22	220	-10		40	1G	12	H	121	1M		
CT	MZ	HT	Y	Radial	Lead Snap in	33	330	+20	R	50	1H	12.5	I	130	1C		
CE	TB	HV				47	470	-0		63	1J	13	J	131	1P		
CP	TP	HL	W	Lug	Snap in Terminal	100	101	+50	T	80	1K	16	K	140	1D		
CH	WL	HF				220	<b>221</b>	-10		100	2A	18	L	144	1Q		
CU	WJ	HX	G	Lug	G Type Terminal	330	331	+75	U	125	2B	20	M	150	1E		
CL	WG	KP				470	471	-10		160	2C	22	N	155	1N		
CF	TL	MP	V	Lug	V Type Terminal	1000	102	+20	V	180	2M	25	O	157	1R		
CK	TZ	GP				2200	222	-10		200	2D	30	P	160	1F		
CZ	TC	RP	S	Screw	Screw Terminal Type	3300	332	+20	H	250	2E	35	Q	170	1G		
CD	TH	XP				4700	472	-5		315	2F	40	R	180	1I		
CJ	TX	BP	M	Chip	Surface Mount Type	10000	103	+30	F	330	2U	51	V	190	1J		
CB	TJ	FP				22000	223	-0		350	2V	64	1	196	1S		
SV	TF	EP				33000	333	+100	W	400	2G	77	2	215	1L		
ST	TA		47000	473	-10	450	2W	90		3	236	1T					
NT	WB									500	2H						

Code	Description
E	PET Sleeve