







ROHS compliant



**NOTES:**

**1.MECHANICAL:**

- 1> Operation force: 1000gf Max.
- 2> Operation Temperature: -30 °C to +85°C.
- 3> Storage Temperature: -40 °C to +85°C.
- 4> Mechanical Life: 3000 cycles operations.
- 5> Resistance to Soldering: 260 ±5°C for 3-5 Seconds.
- 6> Please keep switch in "OFF" when welding.


**2.MATERIAL:**

- 1> Base: UL94V-0 PBT Thermoplastic / Color:Black.
- 2> COVER: UL94V-0 PBT Thermoplastic / Color:Red, Black, Blue.
- 3> ACTUATOR: UL94V-0 PBT High Thermoplastic / Color: White.
- 4> TERMINAL: Copper alloy with gold plating for1.5u".

**3.ELECTRICAL:**

- 1> Non-switching Rating:100mA at 50VDC.
- 2> Switching Rating: 25mA at 24VDC.
- 3> Contact Resistance: Initial 50mΩ Max. Contact Resistance: After life 100mΩ Max.
- 4> Insulation Resistance:100MΩ Min at 500VDC.
- 5> Dielectric Strength: 500VAC for 60seconds.
- 6> Switch Capacitance: 5PF Max at 1MHZ.

**4.PART NUMBER DESCRIPTION:**



**5.PACKING: 29pcs/Tube, 928pcs/Box.**

Drawing	DKG	Date	2018.01.20	LINER	ANGLES	PRODUCT Family DP Series Pitch 2.54mm
Check	TOM	Scale	3:1	>0±0.05	>0° ±0.5°	PRAT NO. DP-06-R-T
Approved		Unit	MM	>1±0.10	>5° ±1.0°	FILE NO. SK-DP-006-A
Size	A4	Rev.	A	>10±0.30		PROJECTION

东莞市康深电子科技有限公司  
Kongshen Electronics technology co., LTD.

REV.	ECN NO.	DRAWN	DATE