



Specifications:

- Voltage rating:50V AC/DC
- 50V AC/DC
- Current rating:0.5A AC/DC
- 0.5A AC/DC
- Withstanding voltage:500V AC/minute
- 150V AC/
- Temperature range:-25 +85
- 25 +85
- Insulation resistance:≥500MΩ
- 500MΩ
- Contact resistance:≤55mΩ
- ≤20mΩ
- After environmental testing:≤40mΩ
- ≤40

X0802 W V S-XX X X S-LP V01  
 ○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○ ○

- 1.Series No
- 2.Category:W-WAFER
- 3.Welding Board Angle:V-180°
- 4.Welding Way:S-SMT
- 5.Row No-Pin No:XXP
- 6.Female Height:A:3.75mm;
- 7.Male Height:D:1.2mm;
- 8.special No:S-With positioning Column
- 9.Material:LP-LCP
- 10.Metal plating:Gold Flash

MATED HEIGHT
X0802WVS-XXXXS-LPV01
Single high
X0802WVS-XXXXS-LPV01

NO.of contacts	Dimensions			
	A	B	C	D
40	21.80	15.20	16.80	20.20
50	25.80	19.20	20.80	24.20
60	29.80	23.20	24.80	28.20
80	37.80	31.20	32.80	36.20
100	45.80	39.20	40.80	44.20
120	53.80	47.20	48.80	52.20
140	61.80	55.20	56.80	60.20
160	69.80	63.20	64.80	68.20
180	77.80	71.20	72.80	76.20
200	85.80	79.20	80.80	84.20

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
MARK					L > 63 ±0.5
REVISIONS					
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					



DSND		SCALE: N/A
DWN		VIEW:
CHKD		UNIT: mm/in
APPD		SIZE: A4

MODEL TYPE:		
PART NO.:		
0.80mm IDC Style Connectors		
DWG NO.:		
X0802WVS-XXXXS-LPV01		
WEIGHT	SHEET	REVISION
	1/1	A0

XKB INDUSTRIAL PRECISION CO.,LIMITED