


REVISION RECORD

REV	ECN	DESCRIPTION	DRFT	DATE

(W/O COVER)



NOTES1:

UL Standard




1. Rated voltage/current : 600V / 40A
2. Torque value : M4 , 10.53Lb.in
3. Wire range : 18~10AWG

NOTES2:

1. Dimension shall be interpreted per ASME Y14.5-2009
2. Pitch : 13.00mm, Poles : N=02~20P
3. Stripping length : 8~9mm
4. Withstanding voltage : AC2200V/1Min
5. Operating temperature : -40°C~+105°C
6. Undimensioned tolerances:

Pitch range in mm	Nominal dimension range in mm							0.1/10
	Over 6 TO 10	Over 10 TO 24	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	±2'	
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2'


7. RoHS Compliance



DBT40C-13.0 - XXP - 1Y - 00A (H)

(Series No.) (Poles) (Single Pitch) (Color): 1.(Grey)
 2.(Blue)
 3.(Black)
 4.(Green)
 5.(Orange)
 6.(Red)
 7.(Transparent)
 8.(Yellow)
 9.(White)

(RoHS)
 00A-(Standard)



PCB LAYOUT

DETACHED LISTS	PART NO.:	/			
	APPD:	/			
	CHKD:	/			
	DRFT:	/			
		<p>THIRD ANGLE PROJECTION</p>		<p>DORABO 慈溪市地博电子有限公司 CIXI DORABO ELECTRONICS CO.,LTD</p>	
		NAME:		DBT40C-13.0-XXP-1Y-00A(H)	
		TITLE:	CUSTOMER DRAWING	REV	D0
		DRAWING NO.:	/	SHEET	1/1
		MM (INCH)	DO NOT SCALE DRAWING	SCALE	1:1