


版次 (Version)	变更内容 (Rev. Content)	变更者 (Change Person)

技术参数 (Technical Data)		
项目 (Item)	UL	IEC
额定电气参数 (Rated Electrical Parameters)	300V/30A	450V/32A
压线范围 (Wire Range)	26~10AWG	4.0mm ²
工频耐压 (Frequency Voltage)	AC 2500V	
冲击耐压 (Rated Surge Voltage)	4000V	
绝缘阻抗 (Insulation Resistance)	DC500V 500MΩ above	
接触电阻 (Contact Resistance)	≤20mΩ	
剥线长度 (Stripping Length)	8mm	
工作温度 (Temperature)	-40°C~+105°C	
材质和电镀 (Material and plating)		
绝缘材质 (Housing)	PA66 (UL94 V-0)	
触点材料 (Contact)	铜合金, 镀锡 (Copper alloy, Sn plated)	
螺丝 (Screws)	钢, 镀锌 (Steel, Zn plated)	
方盒 (Cage)	铜合金, 镀镍 (Copper alloy, Ni plated)	

产品命名编码:
(Product Number Code):

GS008-6.35-XXP-1Y-00A (H)



1: 单倍间距 (Single Pitch)	2: 双倍间距 (Double Pitch)	7: 透明色 (Transparent)	8: 白色 (White)	9: 黄色 (Yellow)	Y: 多种颜色 (Mixed Color)
3: 黑色 (Black)	4: 灰色 (Grey)	5: 橙色 (Orange)	6: 红色 (Red)		

P=6.35mm, N为孔位数 (N for hole digits), 有效位数为 (Significant Digits): 02P, 3P~XXP

N	02P	03P	04P	05P	06P	07P	08P	09P	10P	11P	12P	13P
L	12.70	19.05	25.40	31.75	38.10	44.45	50.80	57.15	63.50	69.85	76.20	82.55
B	6.35	12.70	19.05	25.40	31.75	38.10	44.45	50.80	57.15	63.50	69.85	76.20
N	14P	15P	16P	17P	18P	19P	20P	21P	22P	23P	24P	...
L	88.90	95.25	101.60	107.95	114.30	120.65	127.00	133.35	139.70	146.05	152.40	
B	82.55	88.90	95.25	101.60	107.95	114.30	120.65	127.00	133.35	139.70	146.05	

GOOSVN 宁波高胜电子有限公司
NINGBO GOOSVN ELECTRONIC CO.,LTD

型号 (Type): GS008-6.35-XXP-1Y-00A (H)

核准 (Approval): _____ 图号 (Drawing NO.): _____

审核 (Audit): _____ 单位 (Units): mm 页码 (Page): 1/1

设计 (Design): _____ 比例 (Scale): FULL

公差范围 (Tolerance Range): 150~ ±1.50, 60~150 ±1.00, 30~60 ±0.60, 6~30 ±0.40, 0~6 ±0.25

角度 (Angle): X ±2°, XX ±1°

版次 (Version): T0