





PRODUCT NO.	RoHS compliant
DSDP01LHGETR	


REV.	ECN NO.	DR	DATE



**P.C.B LAYOUT**

- Note:**
- All dimensions are in millimeters.
  - General tolerance:  $\pm 0.2\text{mm}$ .
  - Material:
    - Base: UL94V-0 PBT Thermoplastic (Black).
    - Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
    - Actuators: UL94V-0 PBT Thermoplastic (White).
    - Contact plating: Gold plating over nickel.
    - Pitting material: Epoxy.
  - Electrical
    - Electrical: 2000 Operations per switch 24/VDC, 25mA.
    - Non-Switching Rating: 100mA, 50/VDC.
    - Switching Rating: 25mA, 24/VDC.
    - Contact Resistance: 100 m $\Omega$  Max. at initial.
  - Mechanical
    - Mechanical life: 2000 Operations per switch.
    - Stroke: 30°.
    - Operation Temp: -20°C to 70°C.
    - Storage Temp: -40°C to 85°C.

**6. PART NUMBER DESCRIPTION:**



- 注意:**
- 波峰焊: 推荐焊锡温度在270°C  $\pm$  5°C, 浸锡时间为5~6秒钟。
  - 手工焊: 使用30瓦烙铁控制温度在320°C, 焊接时间大约2~3秒钟。
  - 拨柄位置: 产品焊接时, 请将产品的拨柄置于OFF端, 能给予产品更好的接触性能。
  - 清洗过程: 清洗使用超声波方式, 能给予更好的效果。

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	东莞市广誉实业有限公司 DongGuan Kingtek Industrial Co., Ltd.	
LINER	ANGLES		TITLE	
.0 $\pm$ 0.40	0. $\pm$ 1'	PROJECTION	BY DSDP SERIES PITCH 2.54mm	
.00 $\pm$ 0.30	.0 $\pm$ 0.5'		PRODUCT FAMILY DSDP SERIES	
.000 $\pm$ 0.20	.00 $\pm$	DESIGN LU ER XIN	PRAT NO. DSDP01LHGETR	
DRAWING		2013/07/08	FILE NO. DSDP01LHGETR-A	
CHECK			SIZE A4	UNIT mm
APPD.			SCALE FIT	SHEET 1 OF 1
			REV. A	