




PRODUCT NO.	RoHS compliant
DSDP02LHGETR	

REV.	ECN NO.	DR	DATE



**P.C.B LAYOUT**


**注意:**

1. 波峰焊: 推荐焊锡温度在270℃±5℃, 浸锡时间为5~6秒钟。
2. 手工焊: 使用30瓦烙铁控制温度在320℃, 焊接时间大约2~3秒钟。
3. 拨柄位置: 产品焊接时, 请将产品的拨柄置于OFF端, 能给予产品更好的接触性能。
4. 清洗过程: 清洗使用超音波方式, 能给予更好的效果。

**Note:**

1. All dimensions are in millimeters.
2. General tolerance: ±0.2mm.
3. Material:
  - Base: UL94V-0 PBT Thermoplastic (Black).
  - Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
  - Actuators: UL94V-0 PBT Thermoplastic (White).
  - Contact plating: Gold plating over nickel.
  - Pitting material: Epoxy.
4. Electrical
  - Electrical: 2000 Operations per switch 24/VDC, 25mA.
  - Non-Switching Rating: 100mA, 50/VDC.
  - Switching Rating: 25mA, 24/VDC.
  - Contact Resistance: 100 mΩ Max. at initial.
5. Mechanical
  - Mechanical life: 2000 Operations per switch.
  - Stroke: 30°.
  - Operation Temp: -20℃ to 70℃.
  - Storage Temp: -40℃ to 85℃.

**6. PART NUMBER DESCRIPTION:**



TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES		
.0 ± 0.40	0. ± 1'	PROJECTION	TITLE
.00 ± 0.30	.0 ± 0.5'		BY DSDP SERIES PITCH 2.54mm
.000± 0.20	.00±	DESIGN	PRODUCT FAMILY DSDP SERIES
		LU ER XIN	PRAT NO. DSDP02LHGETR
DRAWING		2013/07/08	FILE NO. DSDP02LHGETR-A
CHECK			SIZE UNIT SCALE SHEET REV.
APPD.			A4 mm FIT 1 OF 1 A