

PRODUCT NO.	RoHS compliant
DSIC12LHGCT	









REV.	ECN NO.	DR	DATE

NOTES :

- 1.Specification:
 - 1>.Operating force:1000gf Max
 - 2>.Operating Temperature:-40° to+85°
 - 3>.Storage Temperature::-40° to+85°
 - 4>.Mechanical Life:3000cycles minimum
 - 5>.Electrical Life:2000cycles 25mA 24VDC

2. PLATING:
 - GOLD FLASH 1u"~2u" SOLDER TAIL,
 - 1u"~3u" GOLD PLATING ON THE CONTACT AREA,
 - WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION



Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED	
				LINER	ANGLES
①	Actuator	UL94 V0	White	.0 ± 0.25	0. ± 2'
②	Cover	UL94 V0	Black	.00 ± 0.15	.0 ± 1'
③	Movable	Copper Alloy	1u"~3u"Gold	.000± 0.10	.00± 0.5'
④	Terminal	Brass	1u"~2u"Gold		
⑤	Base	UL94 V0	Black		
⑥	Terminal Contact	Brass	1u"~3u"Gold		

INSPECTION COPY	PROJECTION	DESIGN	DRAWING	CHECK	APPRO.
		kathy			
		2012/04/12			

TITLE					
BY DSIC SERIES PITCH 2.54mm					
PRODUCT FAMILY DSIC SERIES					
PRAT NO. DSIC12LHGCT					
FILE NO. DSIC12LHGCT-A					
SIZE	UNIT	SCALE	SHEET	REV.	
A4	mm	2 : 1	1 OF 1	A	