





1		2		3		4		5		6	
PRODUCT NO.	RoHS compliant							REV.	ECN NO.	DR	DATE
DSIC12LSGET											

- NOTES :
- Specification:
    - Operating force: 1000gf Max
    - Operating Temperature: -40° to +85°
    - Storage Temperature: -40° to +85°
    - Mechanical Life: 3000cycles minimum
    - Electrical Life: 2000cycles minimum

2. PLATING:  
 GOLD FLASH 1u"~2u" SOLDER TAIL,  
 1u"~3u" GOLD PLATING ON THE CONTACT AREA,  
 WITH 50u" NICKEL UNDERPLATING OVERALL.


3. PART NUMBER DESCRIPTION

DSIC XX L S G E T  
 [包装方式: T=管装 R=Reel]  
 [电镀层: E=接触部 1u"~3u" / 焊尾部 1u"~2u"]  
 [G=镀金 S=内金外镍]  
 [脚型: S脚 / J脚 / H脚 / A脚 / Z脚]  
 [T=低推贴胶 S=低推不贴胶 L=长推]  
 [产品数: 02=2P ..... 08=8P 10=10P 12=12P]




RECOMMENDED P.C.B. LAYOUT (TOP VIEW)


[Schematic]



[焊接行程]



(Construction)



Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED	
				LINER	ANGLES
①	Actuator	UL94 V0	White	.0 ± 0.25	0. ± 2'
②	Cover	UL94 V0	Black	.00 ± 0.15	.0 ± 1'
③	Movable	Copper Alloy	1u"~3u"Gold	.000± 0.10	.00± 0.5'
④	Terminal	Brass	1u"~2u"Gold		
⑤	Base	UL94 V0	Black		
⑥	Terminal Contact	Brass	1u"~3u"Gold		

INSPECTION	COPY
PROJECTION	
DESIGN	kathy
DRAWING	
CHECK	
APPRO.	

**KE** 东莞市广普实业有限公司  
 DongGuan Kingtek Industrial Co., Ltd.

TITLE: BY DSIC SERIES PITCH 2.54mm

PRODUCT FAMILY: DSIC SERIES

PRAT NO.: DSIC12LSGET

FILE NO.: DSIC12LSGET-A

SIZE	UNIT	SCALE	SHEET	REV.
A4	mm	2 : 1	1 OF 1	A

A

B

C

D

A

B

C

D