







1		2		3		4		5		6	
PRODUCT NO.	RoHS compliant							REV.	ECN NO.	DR	DATE
DSPV07LHGET											

NOTES : 1.Specification:  
 1>.Operating force:1000gf Max  
 2>.Operating Temperature:-40° to+85°  
 3>.Storage Temperature: -40° to+85°  
 4>.Mechanical Life:3000cycles minimum  
 5>.Electrical Life:2000cycles minimum



2. PLATING:  
 GOLD FLASH 1u"~2u" SOLDER TAIL,  
 1u"~3u" GOLD PLATING ON THE CONTACT AREA,  
 WITH 50u" NICKEL UNDERPLATING OVERALL.
3. CONTACT RATING:  
 1.SWITCHING:25mA at 24VDC  
 2.NON-SWITCHING:100mA at 50VDC  
 WITH 50u" NICKEL UNDERPLATING OVERALL.

4. PART NUMBER DESCRIPTION :



Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	东莞市广誉实业有限公司 DongGuan Kingtek Industrial Co., Ltd.
				LINER	ANGLES		
①	Actuator	UL94 V0	White	.0 ± 0.25	0. ± 2°	PROJECTION	TITLE
②	Cover	UL94 V0	Black	.00 ± 0.15	.0 ± 1°		BY DSPV SERIES PITCH 2.54mm
③	Movable	Copper Alloy	1u"~3u" Gold	.000± 0.10	.00± 0.5°		PRODUCT FAMILY DSPV SERIES
④	Terminal	Brass	1u"~2u" Gold	DESIGN	kathy		03/20/12'
⑤	Base	UL94 V0	Black	DRAWING			FILE NO. DSPV07LHGET-A
⑥	Terminal Contact	Brass	1u"~3u" Gold	CHECK			SIZE UNIT SCALE SHEET REV.
				APPRO.			A4 mm 1 : 1 1 OF 1 A