

NOTE:

MATERIAL

HOUSING: PBT

CONTACT: C2700.

CONTACT PLATING: 镀金.

ELECTRICAL

CURRENT RATING: 3AMP.

DIELECTRIC WITHSTANDING VOLTAGE: 600VAC MIN.

CONTACT RESISTANCE: 20mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN.




ENVIRONMENTAL

TEMPERATURE RANGE: -40° C TO +105° C.

DIMENSION TABLE

注: 1*40P A尺寸不用减去0.25mm

Circuits	Dimension		Circuits	Dimension		Circuits	Dimension	
	A	B		A	B		A	B
1 * 2	5.08	2.54	1 *15	38.10	35.56	1 *28	71.12	68.58
1 * 3	7.62	5.08	1 *16	40.64	38.10	1 *29	73.66	71.12
1 * 4	10.16	7.62	1 *17	43.18	40.64	1 *30	76.20	73.66
1 * 5	12.70	10.16	1 *18	45.72	43.18	1 *31	78.74	76.20
1 * 6	15.24	12.70	1 *19	48.26	45.72	1 *32	81.28	78.74
1 * 7	17.78	15.24	1 *20	50.80	48.26	1 *33	83.82	81.28
1 * 8	20.32	17.78	1 *21	53.34	50.80	1 *34	86.36	83.82
1 * 9	22.86	20.32	1 *22	55.88	53.34	1 *35	88.90	86.36
1 *10	25.40	22.86	1 *23	58.42	55.88	1 *36	91.44	88.90
1 *11	27.94	25.40	1 *24	60.96	58.42	1 *37	93.98	91.44
1 *12	30.48	27.94	1 *25	63.50	60.96	1 *38	96.52	93.98
1 *13	33.02	30.48	1 *26	66.04	63.50	1 *39	99.06	96.52
1 *14	35.56	33.02	1 *27	68.58	66.04	1 *40	101.60	99.06



Recommended PCB Layout

ROHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。	类别	针座	品名	CS-1109-1X10(L11.5)	X.	±0.50	材料		单位	mm	SHEET 1 OF 1		
	版本	A/0	设计	李文畅	X.X	±0.20	颜色		比例	1:1	▲	修改内容	修改日期
	制定部门	工程部	绘制	李文畅	X.XX	±0.10	画法		数量		1		
	工程图号	CST-1109	审核	姚培柱	X.XXX	±0.05	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.				2		
	制定日期	2017/11/02	核准	周中湖	X.XXXX	±0.01					3		