



Recommended PCB Layout

NOTE:

MATERIAL

HOUSING: PA6T GLASS-REINFORCED THERMOPLASTIC UL 94V-0.
CONTACT: COPPER ALLOY.
CONTACT PLATING: GOLD OVER NICKEL.

ELECTRICAL

CURRENT RATING: 1AMP.
DIELECTRIC WITHSTANDING VOLTAGE: 500VAC MIN.
CONTACT RESISTANCE: 20mΩMAX.
INSULATION RESISTANCE: 1000MΩMIN.

ENVIRONMENTAL

TEMPERATURE RANGE: -25° C TO +85° C.

DIMENSION TABLE: 注: 1*40P A尺寸不用减去0.25mm

Circuits	Dimension		Circuits	Dimension		Circuits	Dimension	
	A	B		A	B		A	B
1 * 2	4.00	2.00	1 * 15	30.00	28.00	1 * 28	56.00	54.00
1 * 3	6.00	4.00	1 * 16	32.00	30.00	1 * 29	58.00	56.00
1 * 4	8.00	6.00	1 * 17	34.00	32.00	1 * 30	60.00	58.00
1 * 5	10.00	8.00	1 * 18	36.00	34.00	1 * 31	62.00	60.00
1 * 6	12.00	10.00	1 * 19	38.00	36.00	1 * 32	64.00	62.00
1 * 7	14.00	12.00	1 * 20	40.00	38.00	1 * 33	66.00	64.00
1 * 8	16.00	14.00	1 * 21	42.00	40.00	1 * 34	68.00	66.00
1 * 9	18.00	16.00	1 * 22	44.00	42.00	1 * 35	70.00	68.00
1 * 10	20.00	18.00	1 * 23	46.00	44.00	1 * 36	72.00	70.00
1 * 11	22.00	20.00	1 * 24	48.00	46.00	1 * 37	74.00	72.00
1 * 12	24.00	22.00	1 * 25	50.00	48.00	1 * 38	76.00	74.00
1 * 13	26.00	24.00	1 * 26	52.00	50.00	1 * 39	78.00	76.00
1 * 14	28.00	26.00	1 * 27	54.00	52.00	1 * 40	80.00	78.00

RoHS2.0

本图纸知识产权及版权由深圳市永丰盈电子有限公司所有, 未经书面许可不准擅自传阅、复制和修改。本公司保留法律追究的权利。

类别	排针	料号	CS-1127WS-1X3B (L16.2)		
版本	A/0	设计	LIWENCHANG	X.X	±0.40
制定部门	工程部	绘制	LIWENCHANG	X.XX	±0.30
工程图号	CS-1127WS	审核	CHENIMNGBIN	X.XXX	±0.20
制定日期	2020/07/01	核准	CUIMIN	X.XXXX	±0.10

材料		单位	mm	SHEET 1 OF 1	
颜色		比例	1:1	修改内容	修改日期
画法		数量			
CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO., LTD.					
