



Recommended PCB Layout

NOTE:

MATERIAL

HOUSING: PBT/BK UL94V-0

CONTACT: BRASS .

CONTACT PLATING: GOLD PLATING.

ELECTRICAL

CURRENT RATING: 3AMP.

VOLTAGE RATING: 250V AC/DC

DIELECTRIC WITHSTANDING VOLTAGE: 600V AC/minute.

CONTACT RESISTANCE: 20mΩMAX.

INSULATION RESISTANCE: 1000MΩ MIN.

ENVIRONMENTAL

TEMPERATURE RANGE: -40° C TO +105° C.

DIMENSION TABLE:

PIN	A(mm)	B(mm)	C(mm)	PIN	A(mm)	B(mm)	C(mm)
06	15.22	5.08	12.92	22	35.54	25.40	33.24
08	17.76	7.62	15.46	24	38.08	27.94	35.78
10	20.30	10.16	18.00	26	40.62	30.48	38.32
12	22.84	12.70	20.54	30	45.70	35.56	43.40
14	25.38	15.24	23.08	34	50.78	40.64	48.48
16	27.92	17.78	25.62	40	58.40	48.26	56.10
18	30.46	20.32	28.16	44	63.48	53.34	61.18
20	33.00	22.86	30.70	50	71.10	60.96	68.80

ROHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	针座	品名	CS-1200-12(L11.6)	X.	±0.50	材料
版本	A/0	设计	李文畅	X.X	±0.20	颜色
制定部门	工程部	绘制	李文畅	X.XX	±0.10	画法
工程图号	CST-1200	审核	姚培柱	X.XXX	±0.05	
制定日期	2018/04/23	核准	周中湖	X.XXXX	±0.01	

CST 深圳市永丰盈电子有限公司
ShenZhenYongFengYing ELECTRONICS CO., LTD.

SHEET 1 OF 1		
①	修改内容	修改日期
②		
③		