



PCB LAYOUT

NOTE:  
 MATERIAL  
 HOUSING: PBT BK UL94V-0.  
 CONTACT: COPPER NEEDLES (C2680).  
 CONTACT PLATING: GOLD .  
 ELECTRICAL  
 CURRENT RATING: 3AMP.  
 VOLTAGE RATING: 250VAC/DC .  
 CONTACT RESISTANCE: 20mΩMAX.  
 INSULATION RESISTANCE:1000MΩMIN.  
 ENVIRONMENTAL  
 TEMPERATURE RANGE: -40°C TO +105°C.  
 PACKING: BLISTER BOX (吸塑盒) 98PCS/BOX.

DIMENSION TABLE:

PIN	A (mm)	B (mm)	C (mm)	D (mm)
10	31.90	21.68	10.16	18.32
14	36.98	26.76	15.24	23.40
16	39.52	29.30	17.78	26.23
20	44.60	34.38	22.85	31.32
26	52.22	42.00	30.46	38.94
30	57.30	47.08	35.56	44.02
34	62.38	52.16	40.64	49.10
40	70.00	59.78	48.26	56.72
50	82.70	72.48	60.96	69.42
60	95.40	85.18	73.66	82.12
64	100.48	90.26	78.74	87.20

ROHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	针座	品名	CS-1200WS-30 (L16mm 短耳)	X.	±0.50	材料		单位	mm	SHEET 1 OF 1		
版本	A/0	设计	李文畅	X.X	±0.20	颜色		比例	1:1	▲	修改内容	修改日期
制定部门	工程部	绘制	李文畅	X.XX	±0.10	画法	⊕	数量		①		
工程图号	CST-1200WS	审核	姚培柱	X.XXX	±0.05	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.						
制定日期	2018/04/04	核准	周中湖	X.XXXX	±0.01							②

CST 深圳市永丰盈电子有限公司  
ShenZhenYongFengYing ELECTRONICS CO.,LTD.

③		
---	--	--