




A

B

C

D

E



### ■ SPECIFICATIONS

- Voltage rating: 50V AC, DC
- Current rating: 1.0A AC/DC (AWG#28)
- Withstanding Voltage: 500V AC/minute
- Insulation resistance: 1000M Ω min
- Temperature range: -40°C - +105°C
- Contact resistance: 20mΩ

### ■ HOUSING

- Part No: CST-1253-XX
- Poles: 2-20
- Material: PBT+15% Glass Fiber
- Q' TY: 1000 pcs/bag

NO	PART NO	DIMENSION (mm)	
		A	B
2	CST-1253-02	1.00	5.00
3	CST-1253-03	2.00	6.00
4	CST-1253-04	3.00	7.00
5	CST-1253-05	4.00	8.00
6	CST-1253-06	5.00	9.00
7	CST-1253-07	6.00	10.00
8	CST-1253-08	7.00	11.00
9	CST-1253-09	8.00	12.00
10	CST-1253-10	9.00	13.00
11	CST-1253-11	10.00	14.00

NO	PART NO	DIMENSION (mm)	
		A	B
12	CST-1253-12	11.00	15.00
13	CST-1253-13	12.00	16.00
14	CST-1253-14	13.00	17.00
15	CST-1253-15	14.00	18.00
16	CST-1253-16	15.00	19.00
17	CST-1253-17	16.00	20.00
18	CST-1253-18	17.00	21.00
19	CST-1253-19	18.00	22.00
20	CST-1253-20	19.00	23.00

**ROHS 2.0**

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。	类别	HOUSING	品名	CS-1253-XX	X.	±0.50	材料		单位	mm	SHEET 1 OF 1		
	版本	A/0	设计	李文畅	X.X	±0.30	颜色		比例	1:1	▲1	修改内容	修改日期
	制定部门	工程课	绘制	李文畅	X.XX	±0.20	画法		数量		▲1		
	工程图号	CST-1253	审核	姚培柱	X.XXX	±0.10	<b>CST</b> 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.				▲2		
	制定日期	2017-11-20	核准	周中湖	X.XXXX	±0.05					▲3		