




A

B

C

D

E



■ SPECIFICATIONS

- Voltage rating: 50V AC, DC
- Current rating: 1.0A AC/DC (AWG#28)
- Withstanding Voltage: 500V AC/minute
- Insulation resistance: 1000M Ω min
- Temperature range: -40°C - +105°C
- Contact resistance: 20mΩ

■ HOUSING

- Part No: CST-1253-XX
- Poles: 2-20
- Material: PBT+15% Glass Fiber
- Q' TY: 1000 pcs/bag

| NO | PART NO | DIMENSION (mm) | |
|----|-------------|----------------|-------|
| | | A | B |
| 2 | CST-1253-02 | 1.00 | 5.00 |
| 3 | CST-1253-03 | 2.00 | 6.00 |
| 4 | CST-1253-04 | 3.00 | 7.00 |
| 5 | CST-1253-05 | 4.00 | 8.00 |
| 6 | CST-1253-06 | 5.00 | 9.00 |
| 7 | CST-1253-07 | 6.00 | 10.00 |
| 8 | CST-1253-08 | 7.00 | 11.00 |
| 9 | CST-1253-09 | 8.00 | 12.00 |
| 10 | CST-1253-10 | 9.00 | 13.00 |
| 11 | CST-1253-11 | 10.00 | 14.00 |

| NO | PART NO | DIMENSION (mm) | |
|----|-------------|----------------|-------|
| | | A | B |
| 12 | CST-1253-12 | 11.00 | 15.00 |
| 13 | CST-1253-13 | 12.00 | 16.00 |
| 14 | CST-1253-14 | 13.00 | 17.00 |
| 15 | CST-1253-15 | 14.00 | 18.00 |
| 16 | CST-1253-16 | 15.00 | 19.00 |
| 17 | CST-1253-17 | 16.00 | 20.00 |
| 18 | CST-1253-18 | 17.00 | 21.00 |
| 19 | CST-1253-19 | 18.00 | 22.00 |
| 20 | CST-1253-20 | 19.00 | 23.00 |

ROHS 2.0

| | | | | | | | | | | | | | |
|--|------|------------|----|------------|--------|-------|---|--|----|-----|--------------|------|------|
| 本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。 | 类别 | HOUSING | 品名 | CS-1253-XX | X. | ±0.50 | 材料 | | 单位 | mm | SHEET 1 OF 1 | | |
| | 版本 | A/0 | 设计 | 李文畅 | X.X | ±0.30 | 颜色 | | 比例 | 1:1 | ▲1 | 修改内容 | 修改日期 |
| | 制定部门 | 工程课 | 绘制 | 李文畅 | X.XX | ±0.20 | 画法 | | 数量 | | ▲1 | | |
| | 工程图号 | CST-1253 | 审核 | 姚培柱 | X.XXX | ±0.10 | CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD. | | | | ▲2 | | |
| | 制定日期 | 2017-11-20 | 核准 | 周中湖 | X.XXXX | ±0.05 | | | | | ▲3 | | |