



■ SPECIFICATIONS

- Voltage rating: 30V AC/DC
- Current rating: 1.5A, AC, DC
- Withstanding Voltage: 500VAC/minute
- Insulation resistance: 1,000MΩ min
- Temperature range: -40°C to +105°C
- Contact resistance: 20mΩ max

■ HOUSING

- Part No: CS-3805B-05AE
- Poles: 5
- Material: PBT, UL94V-0
- Q' TY: 500, 1000 pcs/bag

■ TERMINAL

- Part No. : CS-3805B-T
- Applicable Wire: #22
- Material: Phos. Bronze
- Finish: Tin plated
- Thickness: 0.30mm
- Q' ty: 5000pcs/Reel

ROHS 2.0

本圖紙知識產權及版權由永丰盈有限公司所有, 未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	HOUSING	品名	CS-3805B-05AE	X.	±0.50	材料		单位	mm	SHEET 1 OF 1		
版本	B/1	设计	李文畅	X.X	±0.40	颜色		比例	1:1	⚠	修改内容	修改日期
制定部门	工程课	绘制	李文畅	X.XX	±0.30	画法	⊕	数量		⚠	修正电性能	2021.03.04
工程图号	CST-3805B	审核	姚培柱	X.XXX	±0.20	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.				⚠		
制定日期	2021-03-04	核准	周中湖	X.XXXX	±0.10					⚠		



深圳市永丰盈电子有限公司
ShenZhenYongFengYing ELECTRONICS CO.,LTD.

⚠	修改内容	修改日期
⚠	修正电性能	2021.03.04
⚠		
⚠		