




④2.54±0.15
⑤5.0±0.20



PCB LAYOUT



NOTE:

MATERIAL

HOUSING: PA6T UL94V-0(耐高温材料)

CONTACT: 黄铜 (H65).

CONTACT PLATING: GOLD.

ELECTRICAL

CURRENT RATING: 3AMP.

VOLTAGE RATING: 250VAC/DC.

DIELECTRIC WITHSTANDING VOLTAGE: 600VAC MIN.

CONTACT RESISTANCE: 20mΩ MAX.

INSULATION RESISTANCE: 1000MΩ MIN.

ENVIRONMENTAL

TEMPERATURE RANGE: -40° C TO +105° C.

DIMENSION TABLE: 注: 2*40 P A尺寸不用减0.25mm

Circuits	Dimension		Circuits	Dimension		Circuits	Dimension	
	A	B		A	B		A	B
2 * 2	5.08	2.54	2 * 15	38.10	35.56	2 * 28	71.12	68.58
2 * 3	7.62	5.08	2 * 16	40.64	38.10	2 * 29	73.66	71.12
2 * 4	10.16	7.62	2 * 17	43.18	40.64	2 * 30	76.20	73.66
2 * 5	12.70	10.16	2 * 18	45.72	43.18	2 * 31	78.74	76.20
2 * 6	15.24	12.70	2 * 19	48.26	45.72	2 * 32	81.28	78.74
2 * 7	17.78	15.24	2 * 20	50.80	48.26	2 * 33	83.82	81.28
2 * 8	20.32	17.78	2 * 21	53.34	50.80	2 * 34	86.36	83.82
2 * 9	22.86	20.32	2 * 22	55.88	53.34	2 * 35	88.90	86.36
2 * 10	25.40	22.86	2 * 23	58.42	55.88	2 * 36	91.44	88.90
2 * 11	27.94	25.40	2 * 24	60.96	58.42	2 * 37	93.98	91.44
2 * 12	30.48	27.94	2 * 25	63.50	60.96	2 * 38	96.52	93.98
2 * 13	33.02	30.48	2 * 26	66.04	63.50	2 * 39	99.06	96.52
2 * 14	35.56	33.02	2 * 27	68.58	66.04	2 * 40	101.60	99.06

RoHS2.0

本圖紙知識產權及版權由深圳市永丰盈电子有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	针座	品名	CS-1107-2*2 (L13.8/18.8)	X.	±0.50	材料		单位	mm	SHEET 1 OF 1		
版本	A/0	设计	李文畅	X.X	±0.20	颜色		比例	1:1	修改内容	修改日期	
制定部门	工程部	绘制	李文畅	X.XX	±0.10	画法		数量				
工程图号	CST-1107	审核	姚培柱	X.XXX	±0.05	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELEECTRONICS CO.,LTD.						
制定日期	2018/04/04	核准	周中湖	X.XXXX	±0.01							

CST 深圳市永丰盈电子有限公司
ShenZhenYongFengYing ELEECTRONICS CO.,LTD.
