


REV.	ECN. NO.	APPD.
A		

NOTES:
 Current Rating:3.0AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:-40°C to +105°C




Contact Material:Brass
 Contact plating:Au or Sn Over Ni
 Insulator Material:PBT or PA6T+30%GF(UL94V-0)




Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE ±0.05)



MTP125-11XXR1



Dimension antitheses list			
ITEM	A	B	D
Standard	3.00	6.00	1.20
Alternate			

X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.		
.X ± 0.20	.X° ± 2°				MAT'L	TITLE: MTP125-11XXR1
.XX ± 0.10	.XX° ± 1°				FINISH	
.XXX ± 0.05	.XXX° ± 0.5°				Q'TY	
PIN HEADER CONNECTOR			APPD: SUNNY	DWG NO.:		
			CHKD: LISA			
			DR: ZOE 2006-11-28		SCALE 1/1	
					SHEET 1/1	
				REV. A		