



REV.	ECN. NO.	APPD.
A		

NOTES:
 Current Rating:3.0AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:-40°C to +105°C



Contact Material:Brass
 Contact plating:Au or Sn Over Ni
 Insulator Material:PA6T+30%GF(UL94V-0)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

MTP125-12XXM1



Dimension antitheses list			
ITEM	D	B	W
Standard	0.60	6.00	7.50
Alternate			

X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.				
.X ± 0.20	.X° ± 2°				MAT'L	PART NO.(INTENDED USE)	TITLE:	
.XX ± 0.10	.XX° ± 1°				FINISH	APPD: SUNNY	DWG NO.:	
.XXX ± 0.05	.XXX° ± 0.5°				Q'TY	CHKD: LISA	MTP125-12XXM1	
PIN HEADER CONNECTOR			DR: ZOE	2006-11-28		SCALE	SHEET	REV.
						1/1	1/1	A