







REVISIONS					
P	LTR	DESCRIPTION		DATE	APVD
	E	REVISED	ECR-17-012605	25DEC2017	YN TK



A-A




B-B



A-A

(175029のみ適用)
(ONLY 175029)




B-B


(175029のみ適用)
(ONLY 175029)

1. 製品規格番号 ; 108-5231, 108-5264
2. 嵌合相手端子型番 ; 173630 他
△3 部分金めっき, 他はニッケルめっき

1. PRODUCT SPECIFICATION NO. ; 108-5231, 108-5264
2. RECEPTACLE CONTACT ; 173630 etc.
△3 SELECTIVE GOLD PLATING, REMAINDER NICKEL PLATING

WIRE RANGE AVS 0.2~0.3mm ² (AWG#24-#22)	INSULATION DIA. 1.4~1.9mmφ	バラ端子型番 LOOSE PIECE NUMBER	仕上げ FINISH	材料 MATERIAL	型番 PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 14JUN2012	 TE Connectivity Ltd.		
		CHK K.BETSUI 14JUN2012			
		APVD K.BETSUI 14JUN2012	NAME		
		PRODUCT SPEC	070 SERIES TAB CONTACT		
		SEE NOTE 1			
		APPLICATION SPEC			
		114-5092	SIZE	CAGE CODE	DRAWING NO
		WEIGHT 0.3 g	A3	00779	C-173633
		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1	REV E

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
10 ≥	: ±0.2
30 ≥	: ±0.25
100 ≥	: ±0.3
ANGLE	: ±3°

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	
MATERIAL	FINISH
SEE TABLE	SEE TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN T.SHINOHARA 14JUN2012
	CHK K.BETSUI 14JUN2012
	APVD K.BETSUI 14JUN2012
	PRODUCT SPEC
	SEE NOTE 1
	APPLICATION SPEC
	114-5092
	WEIGHT 0.3 g
	CUSTOMER DRAWING

DWN T.SHINOHARA 14JUN2012		CHK K.BETSUI 14JUN2012		APVD K.BETSUI 14JUN2012	
				NAME	
				070 SERIES TAB CONTACT	
				SIZE	
				CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
				—	