


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		G2		REVISED PER ECR-14-013846	17SEP2014	NK	DC



- 1 APPLICABLE CONTACT P/N 170046-1, -2, -3, 170096-1, -2, 42640-2, 42731-2, 170095-1, 170213-1, -2, -3, 170183-1, -2, 170187-1, -2, 41450, 41829, 61227-1, 63609-1.
 - 2 GENERAL TOLERANCE: ±0.25.
 - 3 NOT APPLICABLE AWG#10 (5mm²) WIRE CRIMPING CONTACT.
- ⚠️ COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT CARRYING CONNECTION DETAILED IN IEC 60335-1. SECTION 30 (GWT).

端子挿入時(被覆外形3.1の時)
 MATING WITH REC CONTACT
 (EX. WIRE INSULATION DIA 3.1)
 端子型番
 REC CONTACT P/N: 170046-2
 電線
 WIRE: AWG#14 (2mm²)

UL94 V-0, GWT	NATURAL	7-171706-1
UL94V-2 調湿品	自然色	2-171706-1
UL94V-2 MOISTURE ITEM	NATURAL	
タイコエレクトロニクスアンプ韓国製品 Tyco Electronics AMP-KOREA Product	自然色	1-171706-1
UL94V-0	NATURAL	
UL94V-2	赤色	171706-2
UL94V-2	自然色	171706-1
備考	色調	型番
REMARKS	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SATO 04DEC2007														
DIMENSIONS: 単位: 特 mm		CHK S. MANABE 04DEC2007														
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD S. MANABE 04DEC2007	NAME 名称													
<table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±</td></tr> <tr><td>2 PLC</td><td>±</td></tr> <tr><td>3 PLC</td><td>±</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ARTICLES</td><td>±</td></tr> </table>		0 PLC	±	1 PLC	±	2 PLC	±	3 PLC	±	4 PLC	±	ARTICLES	±	PRODUCT SPEC 製品規格		250 AMP IPD POD
0 PLC	±															
1 PLC	±															
2 PLC	±															
3 PLC	±															
4 PLC	±															
ARTICLES	±															
MATERIAL 材料 66ナイロン 66NYLON		APPLICATION SPEC 取付適用規格														
FINISH 仕上		WEIGHT		RESTRICTED TO												
		SIZE A3		CAGE CODE 00779												
		DRAWING NO C-171706		SCALE 尺数 NONE												
		CUSTOMER DRAWING		SHEET 1 OF 1												
				REV G2												