

PCB HOLES(TOP VIEW)
GENERAL TOLERANCE:±0.05mm

NOTES:特性

1.ELECTRICAL CHARACTERS.

1.电气特性

1-1.RATING:DC 30V 0.5A:

1-1.额定值: DC 30V 0.5A

1-2.CONTACT RESISTANCE:≤30mΩ;

1-2.接触电阻: ≤30mΩ

1-3.INSULATION RESISTANCE:≥100MΩ DC 500V

1-3.绝缘电阻: ≥100MΩDC 500V

1-4.WITHSTANDING VOLTAGE:AC 500V 1min;

1-4.待机电压: AC 500V 1min

1-5.LIFE:5,000 CYCLES:

1-5.寿命: 5000次循环

2.MECHANICAL CHARACTERISTICS:


2.机械特性:

2-1.INSERTION&EXTRACTION FORCE:~30N:

2-1.插入和拔出力: ~30N:

2-2.OPERATING TEMPERATURE:-30°C~+70°C;

2-2.0工作温度: -30°C~+70°C;



⑥	PIN		1	BRASS	CuSn
⑤	TERMINAL	3	1	BRASS	CuSn
④	BREAK TERMINAL	2	1	BRASS	CuSn
③	TIP SPRING	1	1	BRONZE	SnSb
②	COVER		1	PPA	BLACK
①	HOUSING		1	PPA	BLACK

XKIB	DSND	SCALE: N/A	MODEL TYPE: DC POWER JACK	
	DWN	VIEW:	PART NO.: DC-005-2.5A-2.0	
	CHKD	UNIT: mm/in	DWG NO.:	
	APPD	SIZE: A4	WEIGHT	SHEET
XKB INDUSTRIAL PRECISION CO.,LIMITED			1/1	A0

广东星坤科技股份有限公司

文件工程章

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	