



### Specifications

Impedance: 75 Ohms  
 Frequency Range: DC~3G  
 VSWR: 1.3MAX  
 Working Voltage: 500V rms @ sea level  
 Insulation Resistance: 5000 Ohms min  
 Temperature Range: -55°C T0 +155°C  
 Relative Temperature: ≤95% (40° C ± 2° C)  
 Drawings products are in line with ROHS standards

NOTE:

DRAWN	Zelin Zhang	2012/11/10	Tolerance	0-6 6-30 30-120 Angular	±0.15 ±0.20 ±0.5 ±2°
CHECKED			View		
APPROVALS	John Kine	12/04.2012	UNIT	MM	1:1

**Dosin Industrial(H.K)Co.Ltd**  
 东莞市德奈五金电子有限公司  
**Dosin Hardware Electronics Co.,Ltd**  
 Name: BNC CONNECTOR DNN  
 SIZE A Product NO. DOSIN-801-0094  
 Date/Time 2012/11/02 CAD FILE D:/company drawings/BD  
 E-mail: dosin2005@163.com  
 dosin\_2005@dosin-china.com  
 Web: http://www.dosin.com  
 TEL: (0086) 769-81153906  
 FAX: (0086) 769-81873836

D	Plastic body	PBT	WHITE	1
C	INSULATOR	POM	NONE	1
B	CONTACT PLATING	BRASS	GOLD	1
A	BDDY	ZINC	NICKEL	2
NO	DESCRIPTION	MATERIAL	FINISHED	QTY

Product NO.		DOSIN-801-0094		
REV	DESCRIPTION	DWN	DATE	APPROVEN
A	First Issue	JIM	2012/11/02	John Kine

Name:		BNC CONNECTOR DNN		
SIZE	Product NO.	DOSIN-801-0094		
Date/Time	CAD FILE	D:/company drawings/BD		
SHEET: 1 OF 1		REV B		