

Ordering Information:

A2008H-2xXP - *** / 2 - *** / 3

1.Part NO.

2.Material:

(blank):Nylon 66,UL94V-0

GWT: Nylon 66,UL94V-0(Beige),IEC 60335-1,5th Edition
Glow Wire Capable.

3.Color:

(blank): White

BL: Blue

BK: Black

RD: Red

YL: Yellow

GN: Green

GY: Gray

SPECIFICATIONS:

Current Rating: 3A AC,DC

Voltage Rating: 250V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 30mΩ Max




Insulation Resistance: 1000MΩ Min

Withstanding Voltage: 1000V AC/minute

Material: Nylon 66,UL94V-0

Ordering Information & Dimensions

Circuits	Dimensions(mm)			Circuits	Dimensions(mm)		
	A	B	C		A	B	C
2x2P	2.00	4.60	3.00	2x12P	22.00	24.60	11.50
2x3P	4.00	6.60	3.00	2x13P	24.00	26.60	11.50
2x4P	6.00	8.60	5.00	2x14P	26.00	28.60	15.60
2x5P	8.00	10.60	5.50	2x15P	28.00	30.60	15.60
2x6P	10.00	12.60	5.50	2x16P	30.00	32.60	15.60
2x7P	12.00	14.60	5.50	2x17P	32.00	34.60	15.60
2x8P	14.00	16.60	11.50	2x18P	34.00	36.60	15.60
2x9P	16.00	18.60	11.50	2x19P	36.00	38.60	15.60
2x10P	18.00	20.60	11.50	2x20P	38.00	40.60	15.60
2x11P	20.00	22.60	11.50				



CJTconn CHANGJIANG CONNECTORS CO.,LTD.

REV	DESCRIPTION	DATE
A5	CHANGE THE SIZE C	2020.11.02
A4	ADD THE SIZE OF 2x2P	2019.05.27
A3	ADD THE COLOR	2019.05.27
A2	NEW RELEASE	2018.06.12
A1	MODIFY DRAWINGS	2016.08.08
A0	NEW RELEASE	2011.04.30

Unit	Scale	Sheet
mm	3:1	1 of 1
DRWN	CHK'D	APPR
Dengchun Yi	Dlankul Wan	Jack Yin
General Tolerances		THIRD ANGLE PROJECTION
x.xx±0.25 x.xxx±0.20 x.xxxx±0.15 ANGLES ±1°		

TITLE		DRAWING NO.	REV
2.00mm PITCH DUAL ROW HOUSING			