


PRODUCT NO.	RoHS compliant
DSDP04LHGETB	

REV.	ECN NO.	DR	DATE




P.C.B LAYOUT

- 注意:**
1. 波峰焊: 推荐焊锡温度在270℃±5℃, 浸锡时间为5~6秒钟。
 2. 手工焊: 使用30瓦烙铁控制温度在320℃, 焊接时间大约2~3秒钟。
 3. 拨柄位置: 产品焊接时, 请将产品的拨柄置于OFF端, 能给予产品更好的接触性能。
 4. 清洗过程: 清洗使用超音波方式, 能给予更好的效果。

- Note:**
1. All dimensions are in millimeters.
 2. General tolerance: ±0.2mm.
 3. Material:
 - Base: UL94V-0 PBT Thermoplastic (Black).
 - Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
 - Actuators: UL94V-0 PBT Thermoplastic (White).
 - Contact plating: Gold plating over nickel.
 - Pitting material: Epoxy.
 4. Electrical
 - Electrical: 2000 Operations per switch 24/VDC, 25mA.
 - Non-Switching Rating: 100mA, 50/VDC.
 - Switching Rating: 25mA, 24/VDC
 - Contact Resistance: 100 mΩ Max. at initial.
 5. Mechanical
 - Mechanical life: 2000 Operations per switch.
 - Stroke: 30°.
 - Operation Temp: -20℃ to 70℃.
 - Storage Temp: -40℃ to 85℃.

6. PART NUMBER DESCRIPTION:



TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES		
.0 ± 0.40	0. ± 1'	PROJECTION	TITLE
.00 ± 0.30	.0 ± 0.5'		BY DSDP SERIES PITCH 2.54mm
.000± 0.20	.00±		PRODUCT FAMILY DSDP SERIES
DESIGN	LU ER XIN		2013/01/08
DRAWING			FILE NO. DSDP04LHGETB-A
CHECK			SIZE UNIT SCALE SHEET REV.
APPD.			A4 mm FIT 1 OF 1 A