



PRODUCT NO.	RoHS compliant
DSDP06LHGETB	

REV.	ECN NO.	DR	DATE



- Note:**
- All dimensions are in millimeters.
 - General tolerance: $\pm 0.2\text{mm}$.
 - Material:
 - Base: UL94V-0 PBT Thermoplastic (Black).
 - Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
 - Actuators: UL94V-0 PBT Thermoplastic (White).
 - Contact plating: Gold plating over nickel.
 - Pitting material: Epoxy.
 - Electrical
 - Electrical: 2000 Operations per switch 24/VDC, 25mA.
 - Non-Switching Rating: 100mA, 50/VDC.
 - Switching Rating: 25mA, 24/VDC.
 - Contact Resistance: 100 m Ω Max. at initial.
 - Mechanical
 - Mechanical life: 2000 Operations per switch.
 - Stroke: 30°.
 - Operation Temp: -20°C to 70°C.
 - Storage Temp: -40°C to 85°C.

6. PART NUMBER DESCRIPTION:



- 注意:**
- 波峰焊: 推荐焊锡温度在 $270^{\circ}\text{C} \pm 5^{\circ}\text{C}$, 浸锡时间为 5~6 秒钟。
 - 手工焊: 使用 30 瓦烙铁控制温度在 320°C , 焊接时间大约 2~3 秒钟。
 - 拨柄位置: 产品焊接时, 请将产品的拨柄置于 OFF 端, 能给予产品更好的接触性能。
 - 清洗过程: 清洗使用超声波方式, 能给予更好的效果。

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	东莞市广普实业有限公司 DongGuan Kingtek Industrial Co., Ltd.
LINER	ANGLES		
.0 ± 0.40	0. ± 1'	PROJECTION	TITLE
.00 ± 0.30	.0 ± 0.5'		BY DSDP SERIES PITCH 2.54mm
.000 ± 0.20	.00 ±		PRODUCT FAMILY DSDP SERIES
DESIGN LU ER XIN	2013/01/08		PRAT NO. DSDP06LHGETB
DRAWING		FILE NO. DSDP06LHGETB-A	
CHECK		SIZE UNIT SCALE SHEET REV.	
APPND.		A4 mm FIT 1 OF 1 A	