

PRODUCT NO.	RoHS compliant
DSDP08LHGETB	

REV.	ECN NO.	DR	DATE

Note:

- All dimensions are in millimeters.
- General tolerance: ±0.2mm.
- Material:

Base:UL94V-0 PBT Thermoplastic (Black).
 Cover:UL94V-0 PBT Thermoplastic (Black/Red/Blue).
 Actuators:UL94V-0 PBT Thermoplastic (White).
 Contact plating:Gold plating over nickel.
 Pitting material:Epoxy.




4. Electrical

Electrical:2000 Operations per switch 24/VDC, 25mA.
 Non-Switching Rating:100mA, 50/VDC.
 Switching Rating:25mA, 24/VDC
 Contact Resistance:100 mΩ Max. at initial.

5. Mechanical

Mechanical life:2000 Operations per switch.
 Stroke:30° .
 Operation Temp:-20°C to 70°C.
 Storage Temp:-40°C to 85°C.

6. PART NUMBER DESCRIPTION:



P.C.B LAYOUT

注意:

- 波峰焊: 推荐焊锡温度在270°C ±5°C, 浸锡时间为5~6秒钟.
- 手工焊: 使用30瓦烙铁控制温度在320°C, 焊接时间大约2~3秒钟.
- 拨柄位置: 产品焊接时, 请将产品的拨柄置于OFF端, 能给予产品更好的接触性能.
- 清洗过程: 清洗使用超音波方式, 能给予更好的效果.

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	东莞市广普实业有限公司 DongGuan Kingtek Industrial Co., Ltd.
LINER	ANGLES		
.0 ± 0.40	0. ± 1'	PROJECTION	TITLE
.00 ± 0.30	.0 ± 0.5'		BY DSDP SERIES PITCH 2.54mm
.000± 0.20	.00±		PRODUCT FAMILY DSDP SERIES
DESIGN LU ER XIN	2013/01/08		PRAT NO. DSDP08LHGETB
DRAWING		FILE NO. DSDP08LHGETB-A	
CHECK		SIZE UNIT SCALE SHEET REV.	
APPD.		A4 mm FIT 1 OF 1 A	