






PRODUCT NO.	RoHS compliant
DSDP09LHGETR	

REV.	ECN NO.	DR	DATE

Note:

- All dimensions are in millimeters.
- General tolerance: $\pm 0.2\text{mm}$.
- Material:
 - Base: UL94V-0 PBT Thermoplastic (Black).
 - Cover: UL94V-0 PBT Thermoplastic (Black/Red/Blue).
 - Actuators: UL94V-0 PBT Thermoplastic (White).
 - Contact plating: Gold plating over nickel.
 - Pitting material: Epoxy.
- Electrical
 - Electrical: 2000 Operations per switch 24/VDC, 25mA.
 - Non-Switching Rating: 100mA, 50/VDC.
 - Switching Rating: 25mA, 24/VDC.
 - Contact Resistance: 100 m Ω Max. at initial.
- Mechanical
 - Mechanical life: 2000 Operations per switch.
 - Stroke: 30°.
 - Operation Temp: -20°C to 70°C.
 - Storage Temp: -40°C to 85°C.

6. PART NUMBER DESCRIPTION:



P.C.B LAYOUT

- 注意:**
- 波峰焊: 推荐焊锡温度在270°C \pm 5°C, 浸锡时间为5~6秒钟.
 - 手工焊: 使用30瓦烙铁控制温度在320°C, 焊接时间大约2~3秒钟.
 - 拨柄位置: 产品焊接时, 请将产品的拨柄置于OFF端, 能给予产品更好的接触性能.
 - 清洗过程: 清洗使用超音波方式, 能给予更好的效果.

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY
LINER	ANGLES	
.0 \pm 0.40	0. \pm 1'	
.00 \pm 0.30	.0 \pm 0.5'	
.000 \pm 0.20	.00 \pm	
DESIGN	LU ER XIN	2013/01/08
DRAWING		
CHECK		
APPND.		

东莞市广普实业有限公司 DongGuan Kingtek Industrial Co., Ltd.	
TITLE BY DSDP SERIES PITCH 2.54mm	
PRODUCT FAMILY DSDP SERIES	
PRAT NO. DSDP09LHGETR	
FILE NO. DSDP09LHGETR-A	
SIZE	UNIT
A4	mm
SCALE	SHEET
FIT	1 OF 1
REV.	REV.
A	A