






| | |
|-------------|-----------------------|
| PRODUCT NO. | 1 2 3 4 5 6 |
| DSHP02TSGER | RoHS compliant |

| | | | |
|------|---------|----|------|
| REV. | ECN NO. | DR | DATE |
| | | | |



NOTES :1.Specification:
 1>.Operating force:1000gf Max
 2>.Operating Temperature: -40° to+85°
 3>.Storage Temperature: -40° to+85°
 4>.Electrical life Life:2000cycles 25mA 24VDC
 5>.Mechanical Life:3000cycles Operations

2. PLATING:
 GOLD FLASH 1u"~2u" Gold SOLDERTAIL,
 1u"~3u" Gold GOLD PLATING ON THE CONTACT AREA,
 WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION :
 DSHP XX T S G E R
 [包装方式: T=管装 R=Reel]
 [电镀层: E=接触部 1u"~3u" 焊脚部 1u"~2u" Gold]
 [G= 镀全金 S= 内镀金(接触部)外镀锡(焊脚部)]
 [脚型: S脚 / J脚 / H脚 / A脚 / Z脚]
 [T= 低推贴胶 S= 低推不贴胶 L=长推]
 [产#P数 :02=2P 04=4P.....08=8P 10=10P 12=12P]



[Schematic]



| Number | Part Name | Material | Finished |
|--------|------------------|------------------|--------------|
| ① | Actuator | UL94 V0 | White |
| ② | Cover | UL94 V0 | Black |
| ③ | Movable | Beryllium Copper | 1u"~3u" Gold |
| ④ | Terminal | Brass | 1u"~2u" Gold |
| ⑤ | Base | UL94 V0 | Black |
| ⑥ | Terminal Contact | Brass | 1u"~3u" Gold |
| ⑦ | Mylar | UL94 V0 | 0.05mm |

| | | |
|--------------------------------------|-----------|-----------------|
| TOLERANCE UNLESS OTHERWISE SPECIFIED | | INSPECTION COPY |
| LINER | ANGLES | PROJECTION |
| .0 ± 0.25 | 0. ± 2' | |
| .00 ± 0.15 | .0 ± 1' | |
| .000± 0.10 | .00± 0.5' | 03/20/12' |
| DESIGN | kathy | |
| DRAWING | | |
| CHECK | | |
| APPRO. | | |

| | | | |
|-----------------------------|------|-------|--------|
| | | | |
| TITLE | | | |
| BY DSHP SERIES PITCH 1.27mm | | | |
| PRODUCT FAMILY DSHP SERIES | | | |
| PRAT NO. DSHP02TSGER | | | |
| FILE NO. DSHP02TSGER-A | | | |
| SIZE | UNIT | SCALE | SHEET |
| A4 | mm | 2 : 1 | 1 OF 1 |
| REV. | A | | |