

| | |
|-------------|----------------|
| PRODUCT NO. | RoHS compliant |
| DSIC05TSGER | |

| | | | |
|------|---------|----|------|
| REV. | ECN NO. | DR | DATE |
| | | | |

NOTES :

1. Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Mechanical Life: 3000cycles minimum
- 5>.Electrical Life: 2000cycles minimum








2. PLATING:

GOLD FLASH 1u"~2u" SOLDER TAIL,
1u"~3u" GOLD PLATING ON THE CONTACT AREA,
WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION

DSIC XX T S G E R

- [包装方式: T=管装 R=Reel]
- [电镀层: E=接触部 1u"~3u" / 焊接部 1u"~2u"]
- [G=镀金 S=内金外镍]
- [脚型: S脚 / J脚 / H脚 / A脚 / Z脚]
- [T=低推贴胶 S=低推不贴胶 L=长推]
- [产品数: 02=2P 08=8P 10=10P 12=12P]



RECOMMENDED P. C. B. LAYOUT (TOP VIEW)

| Number | Part Name | Material | Finished | TOLERANCE UNLESS OTHERWISE SPECIFIED | | INSPECTION COPY |
|--------|------------------|--------------|-------------|--------------------------------------|-----------|--------------------------|
| | | | | LINER | ANGLES | |
| ① | Actuator | UL94 V0 | White | .0 ± 0.25 | 0. ± 2' | PROJECTION 2012/04/12 |
| ② | Cover | UL94 V0 | Black | .00 ± 0.15 | .0 ± 1' | |
| ③ | Movable | Copper Alloy | 1u"~3u"Gold | .000± 0.10 | .00± 0.5' | |
| ④ | Terminal | Brass | 1u"~2u"Gold | | | |
| ⑤ | Base | UL94 V0 | Black | | | |
| ⑥ | Terminal Contact | Brass | 1u"~3u"Gold | | | |
| ⑦ | Mylar | UL94 V0 | 0.05mm | | | |

KE 东莞市广普实业有限公司
DongGuan Kingtek Industrial Co., Ltd.

TITLE: BY DSIC SERIES PITCH 2.54mm

PRODUCT FAMILY DSIC SERIES

PRAT NO. DSIC05TSGER

FILE NO. DSIC05TSGER-A

| | | | | |
|------|------|-------|--------|------|
| SIZE | UNIT | SCALE | SHEET | REV. |
| A4 | mm | 2 : 1 | 1 OF 1 | A |