

PRODUCT NO.	RoHS compliant
DSIC10LSGER	

REV.	ECN NO.	DR	DATE

NOTES :







- Specification:
  - Operating force: 1000gf Max
  - Operating Temperature: -40° to +85°
  - Storage Temperature: -40° to +85°
  - Mechanical Life: 3000cycles minimum
  - Electrical Life: 2000cycles minimum

- PLATING:
  - GOLD FLASH 1u"~2u" SOLDER TAIL,
  - 1u"~3u" GOLD PLATING ON THE CONTACT AREA,
  - WITH 50u" NICKEL UNDERPLATING OVERALL.


3. PART NUMBER DESCRIPTION

DSIC XX L S G E R

- [包装方式: T=管装 R=Reel]
- [电镀层: E=接触部 1u"~3u" / 焊尾部 1u"~2u"]
- [G=镀金 S=内金外镍]
- [脚型: S脚 / J脚 / H脚 / A脚 / Z脚]
- [T=低推贴胶 S=低推不贴胶 L=长推]
- [产品数: 02=2P ..... 08=8P 10=10P 12=12P]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED	
				LINER	ANGLES
①	Actuator	UL94 V0	White	.0 ± 0.25	0. ± 2'
②	Cover	UL94 V0	Black	.00 ± 0.15	.0 ± 1'
③	Movable	Copper Alloy	1u"~3u"Gold	.000± 0.10	.00± 0.5'
④	Terminal	Brass	1u"~2u"Gold		
⑤	Base	UL94 V0	Black		
⑥	Terminal Contact	Brass	1u"~3u"Gold		

INSPECTION	COPY
PROJECTION	
DESIGN	kathy
DRAWING	
CHECK	
APPRO.	

东莞市广普实业有限公司 DongGuan Kingtek Industrial Co., Ltd.			
TITLE			
BY DSIC SERIES PITCH 2.54mm			
PRODUCT FAMILY DSIC SERIES			
PRAT NO. DSIC10LSGER			
FILE NO. DSIC10LSGER-A			
SIZE	UNIT	SCALE	SHEET REV.
A4	mm	2 : 1	1 OF 1 A