

PRODUCT NO.	RoHS compliant
DSIC12THGET	

REV.	ECN NO.	DR	DATE

NOTES :







- Specification:
 - Operating force: 1000gf Max
 - Operating Temperature: -40° to +85°
 - Storage Temperature: -40° to +85°
 - Mechanical Life: 3000cycles minimum
 - Electrical Life: 2000cycles 25mA 24VDC

- PLATING:
 - GOLD FLASH 1u"~2u" SOLDER TAIL,
 - 1u"~3u" GOLD PLATING ON THE CONTACT AREA,
 - WITH 50u" NICKEL UNDERPLATING OVERALL.


3. PART NUMBER DESCRIPTION

DSIC XX T H G E T

- [包装方式: T=管装 R=Reel]
- [电镀层: E=接触部 1u"~3u" / 焊尾部 1u"~2u"]
- [镀金: G=镀金 S=内金外镍]
- [脚型: S脚 / J脚 / H脚 / A脚 / Z脚]
- [T=低推贴胶 S=低推不贴胶 L=长推]
- [产品数: 01=1P 03=3P 12=12P]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	DRAWING CHECK APPRO.	DRAWING	FILE NO.	DongGuan Kingtek Industrial Co., Ltd.				
				LINER	ANGLES					TITLE	SIZE	UNIT	SCALE	SHEET
①	Actuator	UL94 V0	White	.0 ± 0.25	0. ± 2'	PROJECTION			DSIC12THGET-A	A4	mm	2 : 1	1 OF 1	A
②	Cover	UL94 V0	Black	.00 ± 0.15	.0 ± 1'					BY DSIC SERIES PITCH 2.54mm				
③	Movable	Copper Alloy	1u"~3u"Gold	.000± 0.10	.00± 0.5'	2012/04/12			PRAT NO.	DSIC12THGET				
④	Terminal	Brass	1u"~2u"Gold											
⑤	Base	UL94 V0	Black											
⑥	Terminal Contact	Brass	1u"~3u"Gold											
⑦	Marly	UL94 V0	0.05mm											

东莞市广普实业有限公司
DongGuan Kingtek Industrial Co., Ltd.

TITLE	DSIC12THGET			
BY DSIC SERIES PITCH 2.54mm				
PRODUCT FAMILY DSIC SERIES				
PRAT NO.	DSIC12THGET			
FILE NO.	DSIC12THGET-A			
SIZE	UNIT	SCALE	SHEET	REV.
A4	mm	2 : 1	1 OF 1	A