

**Ordering Information:**

A2543H-XP - \*\*\* - WH  
 1            2            3

1.Part NO.

2.Style:


(blank): Type 1

2: Type 2

3.Color:

(blank): Beige

WH: White





**SPECIFICATIONS:**

Current Rating: 4A AC,DC  
 Voltage Rating: 250V AC,DC  
 Temperature Range: -40°C ~ +105°C  
 Contact Resistance: 10mΩ Max  
 Insulation Resistance: 1000MΩ Min  
 Withstanding Voltage: 1000V AC/minute  
 Material: Nylon 66,UL94V-0(White)

**Ordering Information & Dimensions**

Part NO.	Dimensions(mm)	
	A	B
A2543H-2P	2.54	5.68
A2543H-3P	5.08	8.22
A2543H-4P	7.62	10.76
A2543H-5P	10.16	13.30
A2543H-6P	12.70	15.84
A2543H-7P	15.24	18.38
A2543H-8P	17.78	20.92
A2543H-9P	20.32	23.46
A2543H-10P	22.86	26.00
A2543H-11P	25.40	28.54
A2543H-12P	27.94	31.08
A2543H-13P	30.48	33.62
A2543H-14P	33.02	36.16
A2543H-15P	35.56	38.70
A2543H-16P	38.10	41.24
A2543H-17P	40.64	43.78
A2543H-18P	43.18	46.32
A2543H-19P	45.72	48.86
A2543H-20P	48.26	51.40



TYPE 1

TYPE 2

**CJTconn** CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet	TITLE  2.54mm PITCH HOUSING
mm	4:1	1 of 1	
DRWN	CHK'D	APPR	
Dengchun Yi	Dlankul Wan	Jack Yin	DRAWING NO.  A2543H-XP-WH
General Tolerances		THIRD ANGLE PROJECTION	
A1	CHANGE THE DRAWING	2020.09.19	REV A1
A0	NEW RELEASE	2005.05.10	
REV	DESCRIPTION	DATE	